

Data sheet

Ultra-Low Freezer ZLN-UT 500 VIP Smart



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

Advantages of the SMART controller:

- 4,3", clear, full colour touch screen
- LAN, USB ports for data transfer
- multi-segment time and temperature programs
- visual and sound alarm
- internal memory for programs and data storage
- event registry
- user manual for direct download
- Quick change of program parameters
- Alarm Bar
- operating with gloves on



Smart - preview screen



Bank: ING BŚ o/Wodzisław Śl. Nr rachunku: 90 1050 1403 1000 0022 0879 5498 Nr rej. W BDO 000005609


NIP: 647-216-26-87 REGON: 276111984 Sąd Rejonowy w Gliwicach, X Wydział Gospodarczy KRS 0000083696



TECHNICAL DATA

air convection	natural
chamber capacity [I]	482
number of boxes 133x133x50mm [pcs]	352
controller	microprocessor PID
display	4,3" full colour touch screen
insulation type	vacuum - VIP panels
TEMPERATURE	
temperature range [°C]	-8650
temperature resolution every [°C]	0,1
cooling time from +20°C to -80°C [min]	210
heating time in case of power failure -80°C to -60°C [min]	90
temperature fluctuation at -80°C [+/-°C]*	1,4
temperature variation at -80°C [+/-°C]*	3,5
CHAMBER	
door	solid
interior	
C Smart	stainless steel to DIN 1.4016
P Smart	DIN 1.4301
housing	
C Smart	powder coated sheet
P Smart	powder coated sheet

overall dims [mm] /1/	
A width	880
B height	2000
depth C	960
internal dims [mm]	
width D	620
height E	1380
depth F	580
height I	670



shelves (standard max)	4 4
max shelf workload [kg] /2/	10
number of internal chambers	2
max unit workload [kg]	85
weight [kg]	243



NIP: 647-216-26-87 REGON: 276111984 Sąd Rejonowy w Gliwicach, X Wydział Gospodarczy KRS 0000083696



ELECTRICAL PARAMETERS

power supply	230V 50-60Hz
nominal power [W]	2100
refrigerant	R290 / GWP=3 R170 / GWP=6
warranty	24 months
manufacturer	POL-EKO-APARATURA

all the above technical data refer to standard units (without optional accessories)

* - fluctuation measured in centre of the chamber; in space, variation (K) calculated for chamber as:

K= +/- (T average max. - T average min.) / 2

** - other power supplies on request

1 - depth doesn't include 50 mm of power cable

OPTIONS AND ACCESSORIES



