


LABORATORY FREEZER

LF 625 W (White finishing) LF 625 S (Stainless steel finishing)

- Structure: upright type, realized in sheet steel with special anti-bacterial epoxy coating white colour both in- and outside or in stainless steel 18/10 AISI 304 both in- and outside. All the internal corners are rounded to make easy any cleaning operations and the internal bottom is tray type to contain spills
- **Insulation:** high density (40 Kg/m³) foamed-in-place polyurethane, with a thickness of 75 mm. CFC-free
- Feet: Nr 4 made in stainless steel 18/10 AISI 304, adjustable in height for levelling
- Insulated door: Nr 1, hinged, made with the same material and insulation as the rest of the structure (sheet steel with special anti-bacterial epoxy coating white colour or stainless steel 18/10 AISI 304 always both in- and outside). The door is provided with a removable magnetic rubber gasket in order to grant a perfect hermetic closing, the closing profile is heated to avoid the gasket frosting and reversibility facilities, to change the door hanging. The handle is flush-fitting type so does not increase the size of the freezer. The door is also fitted with a spring loaded automatic closing device for openings inferior 90° and special door switch that stops the internal ventilation at the door opening (to limit the air cold loss) and light the internal lighting at every opening
- Internal equipment: Nr 3, storage open wire shelves realized in sheet steel with a strong plastic coating (rust-proof material). The shelves are mounted on special anti-tilt stainless steel slides that allows the shelf extraction and they can be easily removed and adjusted in height without the use of any tool. The special internal racking-system allows a great flexibility of the internal fitting with the possibility of interchange and combine both shelves and drawers (drawers optionally available)
 - Shelf dimensions (W x D cm): 53 x 65
 - Shelf loading capability (Kg): 35 (with uniformly stored material)
- Internal lighting: Nr 1 LED lamp, mounted in the bottom part of the control panel, with automatic activation at every door opening through a special switch
- Control panel: located in the top part of the structure (above the door), it is
 microprocessor operating with 6 soft-touchpads and LED display, allowing the
 control of all the functions and working status of the freezer (including alarms).
 The main functions of the control panel are:
 - LED display, with bright indication, red colour, of the actual internal temperature and enlightened icons in green colour indicating the appliance working status (compressor functioning, defrosting, fan running, etc.)
 - Digital temperature adjusting and displaying with an accuracy of 0,1°C
 - Keyboard buttons with locking protection, manually activable, to avoid tampering from unauthorized persons
 - · Visual and acoustic alarm signalling (with automatic resetting) for:
 - high and low temperature with limits programmable from the user
 - door ajar, delayed to allow the standard operations
 - power failure (at the return of the mains supply)
 - anti-freezing evaporator
 - sensors failure
 - Muting facilities for the acoustic alarms with maintaining of the visual indication of the alarm condition
 - Alarms memory for the last 10 alarm conditions, with the possibility of checking from the display, the sort of alarm, when the alarm is started, when it is ended and which is the highest or lowest peak reached from the temperature (where applicable)
 - Ntc type sensors for a high accuracy of the temperature control
 - NC contact to remote the alarm signals







SCHEDA TECNICA - TECHNICAL SHEET - FICHE TECHNIQUE

LABORATORY FREEZER

- Cooling unit: top mounted, with the condensing unit compounded by Nr 1 hermetic compressors and Nr 1 finned condenser, air cooled through a fan. Also, in the ceiling of the storage chamber, is mounted the finned evaporator with copper pipes, that is housed into a stainless steel cover that incorporate the fan. All the mounted components are industrial grade to grant the maximum reliability
- Refrigerant: R452A CFC-free
- Refrigeration: forced-air, through a fan, granting the maximum temperature uniformity and stability inside of the cabinet
- **Defrosting:** completely automatic, thermostat controlled. The condensate water is automatically channelled into an heated tray, located in the cabinet backside, for the automatic evaporation of the condensate water
- Temperature range: infinitely adjustable between -5°C / -25°C
- Voltage (V/ph/Hz): 220-230/1/50
- Plug: Schuko type (type F+E)
- Breakers: Nr 2 glass cartridge fuses with a rating of 16A, at protection of the appliance
- **Noise level (dB(A)):** ≤ 52
- Gross capacity (litres): 700 (24.71 cu.ft.)
- Net capacity (litres): 625 (22.06 cu.ft.)
- Dimensions (W x D x H cm): $75 \times 82 \times 210$
- Net weight (Kg): 170
- Packed dimensions (W x D x H cm): 85 x 98 x 224 (1,87 m³)
- Gross weight (Kg): 190



LABORATORY FREEZER

ACCESSORIES AVAILABLE



Extra wire shelf



Wire basket



Plastic partitions for drawers



Kit of castors



Temperature chart recorder




Cable port with cover Ø 18 mm



Internal spark-proofing




GSM/GPRS telephone dialer





Extra stainless steel wire shelf



Stainless steel drawer



Front top for drawers



Safety door lock with key



Internal electrical socket



Cable port with cover Ø 45 mm



\$\frac{1}{230V / 60 Hz} Different voltage

Natural refrigerant R290



Wooden crate packing









Product certified as medical device in class IIa Certificate N. 1448/MDD

^{*} The declared performances are referred at +32°C ambient temperature, relative humidity of 70% and without any internal thermal mass (empty

^{*} Should it be necessary or useful without undermining any model essential features, technical and stylistic characteristics are subject to be changed without manufacturer's previous notice.