## SNOL 15/1300 LSC01

High accuracy electric furnace with solid ceramic chamber SNOL 15/1300 is intended for hardening, loosening, normalizing and other thermal processing up to 1300°C. To eliminate gasses or smokes that are released during thermal processing, exhaust system may be additionally installed in the products. The furnace is excellent fit for scientific laboratories, educational institutions, medicine and industry.

## Basic model

- Solid ceramic chamber
- Partially exposed heating elements are in four sides around the chamber
- ✓ Outside casing metal sheet, powder painted grey
- Door opens sideways
- Door safety interlock switch
- Control panel is placed in the underpart of the furnace
- Digital PID temperature controller E5CC (1 program, 2 steps);
- Ceramic bottom plate
- High quality, ecological thermal insulation material
- Low electric power consumption
- Short heating up/cooling down period
- ✓ High degree of accuracy
- 1 year warranty

## Options

- ✓ Fan-assisted chimney for forced air extraction
- ✓ Additional ceramic hearth plates
- Buzzer
- Digital timer for delayed start only
- Protection against overheating
- ✓ Data recorder
- Data communication/USB
- ✓ Calibration of temperature measurement system
- ✓ Table for supporting the furnace
- ✓ Additional 1 year warranty

## Specifications

Volume, L15Maximum temperature, °C1300Continuous operating temperature, °CT+10-1300Power6Rated supply voltage, V400Number of phases3	
Continuous operating temperature, °CT+10-1300Power6Rated supply voltage, V400Number of phases3	
Power6Rated supply voltage, V400Number of phases3	
Rated supply voltage, V400Number of phases3	
Number of phases 3	
Rated frequency, Hz 50/60	
Chamber material Ceramic	
Maximum heating-up time (without charge), min. 140	
Temperature stability 1	
Temperature uniformity 10°C	
Airflow Natural	
Chamber width, mm 215	
Chamber depth, mm 400	
Chamber height, mm 195	
Overall width, mm 640	
Overall depth, mm 680	
Overall height, mm 820	
Mass (Netto), kg 130	

