

Battery Shaker KM 2 Akku



Description

The Battery Shaker KM 2 Akku with orbital motion can be used for various tasks thanks to its off-grid battery with a run time of min. 40 hours. The shaking platform of 200 x 295 mm can be loaded with max. 2 kg. The stroke of the laboratory shaker KM 2 Akku is 20 mm and the shaking speed is between 5 and 220 rpm.

Basic Equipment

Basic device incl. basic platform and rubber mat, with battery charger / power unit

Loading Capacity

Erlenmeyer flasks 10 ml 20 pieces

Erlenmeyer flasks 50 ml 12 pieces

You will find further loading possibilities [here](#)

Details

Motion: orbital

Shaking platform:	200 x 295 mm
Max. load:	2 kg
Shaking speed:	5 - 220 rpm, in steps of 5
Stroke:	20 mm
Battery charging time:	approx. 10 h
Runtime Battery:	min. 40 h
Runtime with mains cable:	0 - 99 h 59 min / continuous
Order No.:	6135 000
Accessory:	Universal tray KM Mini Universal tray KM Clamping strip KM

Technical specifications

Electrical supply battery charger:	100 - 240 V, 50 / 60 Hz
Internal electrical supply:	1 battery 12 V / 7 Ah
Enclosure protection:	IP 21
Heat emission:	approx. 0,5 - 2 W
Ambient temperature:	4°C to 45°C
Relative humidity:	~ 95 % (non-condensing)
Dimensions (w x d x h):	250 x 415 x 145 mm
Weight:	10,5 kg